

Technical data sheet

Reflector

Part no.: 50003188

TK 20x75

Contents

- Technical data
- Dimensioned drawings



Figure can vary

Technical data

Mechanical data

Design	Rectangular
Triple reflector size	2.6 mm
Mounting dimension, width	20.2 mm
Mounting dimension, height	76 mm
Mounting dimension, thickness	6.5 mm
Reflection surface height	70 mm
Reflection surface width	15 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Net weight	8 g
Type of fastening	Rear side can be glued

Certifications

Degree of protection	IP 67
----------------------	-------

Classification

Customs tariff number	90029000
eCl@ss 5.1.4	27279203
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
eCl@ss 10.0	27273601
eCl@ss 11.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467

Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

Dimensioned drawings

All dimensions in millimeters

