

## Technical data sheet

### Reflector

Part no.: 50003189

TK 30x50

#### Contents

- Technical data
- Dimensioned drawings



Figure can vary

## Technical data

### Mechanical data

Design	Rectangular
Triple reflector size	4 mm
Mounting dimension, width	32 mm
Mounting dimension, height	48 mm
Mounting dimension, thickness	6.8 mm
Reflection surface height	45 mm
Reflection surface width	29 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Net weight	8 g
Type of fastening	Rear side can be glued

### Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

### Certifications

Degree of protection	IP 67
----------------------	-------

### Classification

Customs tariff number	90029000
eCl@ss 5.1.4	27279203
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
eCl@ss 10.0	27273601
eCl@ss 11.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467

## Dimensioned drawings

All dimensions in millimeters

