

## Technical data sheet

### Adapter

Part no.: 50109834

KDS BUS OUT M12-T-5P

#### Contents

- Technical data
- Electrical connection
- Accessories



For illustration purposes only

## Technical data

### Basic data

Suitable for interface	MultiNet Plus
	PROFIBUS DP

### Connection

Number of connections	3 Piece(s)
-----------------------	------------

#### Connection 1

Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	5 -pin
Encoding	B-coded
Version	Axial

#### Connection 2

Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	5 -pin
Encoding	B-coded
Version	Axial

#### Connection 3

Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	5 -pin
Encoding	B-coded
Version	Axial

### Mechanical data

Net weight	21 g
------------	------

### Classification

Customs tariff number	85366990
ECLASS 5.1.4	27279201
ECLASS 8.0	27440104
ECLASS 9.0	27069190
ECLASS 10.0	27440111
ECLASS 11.0	27440111
ECLASS 12.0	27440111
ECLASS 13.0	27440111
ECLASS 14.0	27440111
ECLASS 15.0	27440111
ECLASS 16.0	27440111
ETIM 5.0	EC002498
ETIM 6.0	EC002925
ETIM 7.0	EC002925
ETIM 8.0	EC003558
ETIM 9.0	EC003558
ETIM 10.0	EC003558

## Electrical connection

### Connection 1

Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	5 -pin
Encoding	B-coded
Version	Axial

### Connection 2

Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	5 -pin
Encoding	B-coded
Version	Axial

### Connection 3

Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	5 -pin
Encoding	B-coded
Version	Axial

**Accessories****General**

	<b>Part no.</b>	<b>Designation</b>	<b>Article</b>	<b>Description</b>
	50132266	TT-Set 0,6-13	Tool	Type: Torque key Width across flats: 13 mm Torque: 0.6 N·m Material: Plastic, Stainless steel Ambient temperature: -40 ... 120 °C

**Note**

A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.