

Technical data sheet

Reflector

Part no.: 50136383

TKS 40x60.Chem

Contents

- Technical data



Figure can vary

Technical data

Basic data

Area of application	Food
---------------------	------

Mechanical data

Design	Rectangular
Triple reflector size	2.3 mm
Mounting dimension, width	41 mm
Mounting dimension, height	60 mm
Mounting dimension, thickness	8 mm
Reflection surface height	56 mm
Reflection surface width	37 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PET
Lens cover material	Plastic/PET
Structure, active surface	Triple
Net weight	16 g
Type of fastening	Adhesive Through-hole mounting
Compatibility of materials	Alcohol ECOLAB H2O2

Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

Certifications

Degree of protection	IP 67
----------------------	-------

Classification

Customs tariff number	90029000
eCl@ss 5.1.4	27279203
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
eCl@ss 10.0	27273601
eCl@ss 11.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467