


BTP 200M..., BTP 300M...


Mechanical protective cover

Dimensioned drawing

BTP 200M...




BTP 300M...



Tightening torque of the screw terminals M5 < 2.8Nm!

en 02-2014/08 50118537



- Universal, mechanical protection
- Rod mounting \varnothing 10mm, \varnothing 12mm or \varnothing 14mm
- Simple mounting via the installed sensor, also possible retroactively
- Stable metal design

We reserve the right to make changes • DS_AccessoryBTP_en_50118537.fm

Specifications

	BTP 200M...	BTP 300M...
General Specifications		
Mounting	on rod Ø 10mm on rod Ø 12mm on rod Ø 14mm	
Suitable for sensors	3B Series 5 Series 18 Series 25B Series 28 Series 55 Series	8 Series 9 Series 46B Series
Installation together with	BTU 200M-D...	BTU 300M-D...
Mechanical data		
Material	clamp: aluminum diecast sensor holder: zinc-plated steel	
Tightening torque ¹⁾	screw terminals M5 (SW 4): max. 2.8Nm	
1) Screw mounted with washer		

Mounting

- Select mounting location on the rod and clamp mounting device.

Order guide

Sensor series	Rod	Designation	Part No.
3B, 5, 18, 25B, 28, 55	Ø 10mm	BTP 200M-D10	50117830
	Ø 12mm	BTP 200M-D12	50117829
	Ø 14mm	BTP 200M-D14	50117828
8, 9, 46B	Ø 10mm	BTP 300M-D10	50117827
	Ø 12mm	BTP 300M-D12	50117826
	Ø 14mm	BTP 300M-D14	50117825

Remarks

Operate in accordance with intended use!

- ↪ The product may only be put into operation by competent persons.
- ↪ Only use the product in accordance with the intended use.