

## Technical data sheet

### Connector

Part no.: 50132542

S M8A-3P-SK

#### Contents

- Technical data
- Electrical connection



Figure can vary



## Technical data

### Basic data

### Electrical data

#### Performance data

Operating voltage Max. 250 V AC/DC

### Connection

#### Connection 1

Type of connection	Connector
Thread size	M8
Type	Male
Handle body material	Metal
No. of pins	3 -pin
Encoding	A-coded
Version	Axial
Lock	Screw fitting, nickel-plated diecast zinc, recommended torque 0.6 Nm, self-locking

### Mechanical data

Width across flats 9 mm

### Environmental data

### Certifications

Degree of protection IP 67

### Classification

Customs tariff number	85369010
eCl@ss 5.1.4	27279201
eCl@ss 8.0	27440102
eCl@ss 9.0	27060311
eCl@ss 10.0	27440102
eCl@ss 11.0	27440102
ETIM 5.0	EC002635
ETIM 6.0	EC002635
ETIM 7.0	EC002635

## Electrical connection

### Connection 1

Type of connection	Connector
Thread size	M8
Type	Male
Handle body material	Metal
No. of pins	3 -pin
Encoding	A-coded
Version	Axial
Lock	Screw fitting, nickel-plated diecast zinc, recommended torque 0.6 Nm, self-locking

### Pin

1	-
3	-
4	-

### Conductor color

