

## Technical data sheet

### Wireless mobile 2D-code reader

Part no.: 50143088

IT 1952g SR-2-R

#### Contents

- Technical data
- Electrical connection
- Diagrams
- Operation and display
- Notes
- Accessories



Figure can vary



## Technical data

### Basic data

Series	IT19xx
--------	--------

### Read data

Code types, readable	2/5 Interleaved
	Aztec
	Codabar
	Code 128
	Code 39
	Code 93
	Composite Codes
	Data Matrix Code
	DotCode
	EAN 128
	EAN 8/13
	EAN Addendum
	GS1 Databar
	GS1 Databar Expanded
	GS1 Databar Limited
	GS1 Databar Omnidirectional
	GS1 Databar Stacked
	GS1 Databar Truncated
	Maxicode
	Micro PDF
	Micro QR
	Others on request
	PDF417
	QR code
	UPC

### Optical data

Reading distance	0 ... 822 mm
Camera resolution, horizontal	1,280 px
Camera resolution, vertical	800 px

### Electrical data

#### Performance data

Supply voltage $U_B$	4.2 V, DC
Power consumption, max.	2.5 W
Battery technology	Lilon
Battery storage capacity	2.4 A·h

### Interface

Type	PS/2, RS 232, USB
------	-------------------

### RS 232

Function	Process
----------	---------

### USB

Function	Process
----------	---------

### Connection

Bluetooth range	Class 2
Bluetooth version	4.2

#### Connection 1

Type of connection	Bluetooth
--------------------	-----------

### Mechanical data

Dimension (W x H x L)	70 mm x 160 mm x 80 mm
Housing material	Plastic
Plastic housing	UL 94-V0
Net weight	220 g

### Environmental data

Ambient temperature, operation	0 ... 50 °C
Ambient temperature, storage	-40 ... 70 °C
Relative humidity (non-condensing)	0 ... 95 %
Drop height	1.8 m
Measurements relative to	Concrete floor

### Certifications

Degree of protection	IP 41
----------------------	-------

### Classification

Customs tariff number	84719000
ECLASS 5.1.4	27280103
ECLASS 8.0	27280103
ECLASS 9.0	27280103
ECLASS 10.0	27280103
ECLASS 11.0	27280103
ECLASS 12.0	27280103
ECLASS 13.0	27280103
ETIM 5.0	EC002550
ETIM 6.0	EC002999
ETIM 7.0	EC002999
ETIM 8.0	EC002999

## Electrical connection

### Connection 1

Function	Configuration interface
	Data interface
Type of connection	Bluetooth

## Diagrams

### Typical reading behavior

	A [mil]	B [mm]	C [mm]	D [mm]
Code 39	3	0,076	56	132
	5	0,127	28	242
	10	0,254	0	443
	20	0,508	4	822
UPC	13	0,330	0	490
Code 128	7,5	0,191	25	295
	15	0,381	0	543
PDF 417	5	0,127	54	160
	6,7	0,170	34	220
DM	7,5	0,191	49	172
	10	0,254	29	245
QR	10	0,254	35	250
	20	0,508	0	438

A Module size [mil]  
 B Modulus size [mm]  
 C From [mm]

D To [mm]  
**ATTENTION** Please observe the note below  
 ! regarding the reading distances.

## Operation and display

LED	Display	Meaning
1	Red, continuous light	Low battery level
	Green, 1x flashing	Reading successful
	Red, flashing	Communication error

## Notes




**Observe intended use!**



- ⚠ This product is not a safety sensor and is not intended as personnel protection.
- ⚠ The product may only be put into operation by competent persons.
- ⚠ Only use the product in accordance with its intended use.


## Accessories

### Connection technology - Connection unit


	Part no.	Designation	Article	Description
	50112891	MA 248i Profinet Gateway	Modular connection unit	Supply voltage: 18 ... 30 V Current consumption, max.: 300 mA Interface: PROFINET, RS 232 Connections: 6 Piece(s) Degree of protection: IP 65

## Accessories


### Connection technology - Base stations

	Part no.	Designation	Article	Description
	50143593	Base IT 1952g	Base station	Interface: USB, PS/2, RS 232 Bluetooth range: Class 2 Bluetooth version: 4.2 Connection 1: RJ41 Connection 2: Jack socket Connection 3: Bluetooth


### Connection technology - Connection cables

	Part no.	Designation	Article	Description
	50113397	KB JST-HS-300	Connection cable	Suitable for interface: RS 232 Connection 1: JST ZHR Connection 2: Sub-D, Axial, Male, 9 -pin Shielded: Yes Cable length: 300 mm Sheathing material: PUR

### Connection technology - Interconnection cables

	Part no.	Designation	Article	Description
	50114517	KB 232-1 IT190x	Interconnection cable	Suitable for interface: RS 232, TTL Connection 1: RJ41 Connection 2: Sub-D, Axial, Female, 9 -pin Connection 3: Connector, Pluggable, Axial, Female, 2 -pin Shielded: Yes Cable length: 3,000 mm Sheathing material: PVC

### Replacement part

	Part no.	Designation	Article	Description
	50105384 **	Battery IT-series	Battery	Supply voltage: 3.7 V, DC Battery technology: Lilon Battery storage capacity: 2.4 A·h

\*\* Included in delivery contents

#### Note



A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.