

Technical data sheet Interconnection cable

Part no.: 150683

CB-M12-5000-3GF/WM

Contents

- Technical data
- Electrical connection
- Circuit diagrams




Figure can vary



Technical data

Electrical data

Performance data

Operating voltage	30 V AC/DC
-------------------	------------

Connection

Connection 1

Type of connection	Connector
--------------------	-----------

Thread size	M12
-------------	-----

Type	Female
------	--------

Handle body material	TPU
----------------------	-----

No. of pins	3 -pin
-------------	--------

Version	Axial
---------	-------

Operating current per contact	4 A
-------------------------------	-----

Lock	Screw fitting
------	---------------

Connection 2

Type of connection	Connector
--------------------	-----------

Thread size	M12
-------------	-----

Type	Male
------	------

Handle body material	TPU
----------------------	-----

No. of pins	3 -pin
-------------	--------

Version	Angled
---------	--------

Operating current per contact	4 A
-------------------------------	-----

Cable properties

Number of conductors	3 Piece(s)
----------------------	------------

Wire cross section	0.34 mm ²
--------------------	----------------------

Sheathing color	Black
-----------------	-------

Shielded	No
----------	----

Cable design	Interconnection cable
--------------	-----------------------

Cable diameter (external)	4.3 mm
---------------------------	--------

Cable length	5,000 mm
--------------	----------

Conductor material	Copper
--------------------	--------

Sheathing material	PUR
--------------------	-----

Suitability for drag chains	No
-----------------------------	----

Environmental data

Ambient temperature, operation, stationary use	-25 ... 80 °C
--	---------------

Classification

Customs tariff number	85444290
-----------------------	----------

eCl@ss 5.1.4	27279201
--------------	----------

eCl@ss 8.0	27279218
------------	----------

eCl@ss 9.0	27060311
------------	----------

eCl@ss 10.0	27060311
-------------	----------

eCl@ss 11.0	27060311
-------------	----------

ETIM 5.0	EC001855
----------	----------

ETIM 6.0	EC001855
----------	----------

ETIM 7.0	EC001855
----------	----------

Electrical connection

Connection 1

Type of connection	Connector
--------------------	-----------

Thread size	M12
-------------	-----

Type	Female
------	--------

Handle body material	TPU
----------------------	-----

No. of pins	3 -pin
-------------	--------

Version	Axial
---------	-------

Operating current per contact	4 A
-------------------------------	-----

Lock	Screw fitting
------	---------------

Connection 2

Type of connection	Connector
--------------------	-----------

Thread size	M12
-------------	-----

Type	Male
------	------

Handle body material	TPU
----------------------	-----

No. of pins	3 -pin
-------------	--------

Version	Angled
---------	--------

Operating current per contact	4 A
-------------------------------	-----

Circuit diagrams

Wiring schematic

