

## Technical data sheet

### Mounting system

Part no.: 50117253

BTU 300M-D10

#### Contents

- Technical data
- Dimensioned drawings



For illustration purposes only

## Technical data

### Basic data

<b>Contains</b>	2x M4 x 20 screw
	2x M4 x 25 screw
	4x position washers
<b>Suitable for product group</b>	Optical distance sensors Switching sensors, cubic
<b>Suitable for</b>	10 series sensors 25C series sensors 46B series sensors 46C series sensors 8 series sensors ODSL 9

### Mechanical data

<b>Standard designation, metal mounting device</b>	Aluminum
	Steel, galvanized
<b>Net weight</b>	59 g
<b>Design of mounting device</b>	Mounting system
<b>Type of fastening, at system</b>	For 10 mm rod
	Sheet-metal mounting
<b>Type of fastening, at device</b>	Screw type
	Suited for M4 screws
<b>Type of mounting device</b>	Adjustable
	Clampable
	Turning, 360°
<b>Mounting device material</b>	Metal

### Classification

<b>Customs tariff number</b>	73182900
<b>ECLASS 5.1.4</b>	27279202
<b>ECLASS 8.0</b>	27279202
<b>ECLASS 9.0</b>	27273701
<b>ECLASS 10.0</b>	27273701
<b>ECLASS 11.0</b>	27273701
<b>ECLASS 12.0</b>	27273701
<b>ECLASS 13.0</b>	27273701
<b>ECLASS 14.0</b>	27273701
<b>ECLASS 15.0</b>	27273701
<b>ECLASS 16.0</b>	27273701
<b>ETIM 5.0</b>	EC002498
<b>ETIM 6.0</b>	EC003015
<b>ETIM 7.0</b>	EC003015
<b>ETIM 8.0</b>	EC003015
<b>ETIM 9.0</b>	EC003015
<b>ETIM 10.0</b>	EC003015
<b>UNSPSC 26.08</b>	31242100

## Dimensioned drawings

All dimensions in millimeters

