

## Technical data sheet

### Reflective tape

Part no.: 50111772

REF 4-A-50x45700

#### Contents

- Technical data



For illustration purposes only

## Technical data

### Mechanical data

|  |               |
|--|---------------|
| Design                                   | Rectangular   |
| Direction independent                    | Yes           |
| Mounting dimension, width                | 50 mm         |
| Mounting dimension, height               | 45,700 mm     |
| Reflective surface, height               | 45,700 mm     |
| Reflective surface, width                | 50 mm         |
| Reflective surface width, tolerance      | ± 1 mm        |
| Reflector material                       | Plastic       |
| Polarization-changing                    | Yes           |
| Chemical designation, reflector material | PMMA          |
| Structure, active surface                | Triple        |
| Net weight                               | 1,020 g       |
| Type of fastening                        | Self-adhesive |

### Environmental data

|                                |               |
|--------------------------------|---------------|
| Ambient temperature, operation | -40 ... 80 °C |
|--------------------------------|---------------|

### Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 39191080 |
| ECLASS 5.1.4          | 27279203 |
| ECLASS 8.0            | 27279203 |
| ECLASS 9.0            | 27273601 |
| ECLASS 10.0           | 27273601 |
| ECLASS 11.0           | 27273601 |
| ECLASS 12.0           | 27273601 |
| ECLASS 13.0           | 27273601 |
| ECLASS 14.0           | 27273601 |
| ECLASS 15.0           | 27273601 |
| ETIM 5.0              | EC002467 |
| ETIM 6.0              | EC002467 |
| ETIM 7.0              | EC002467 |
| ETIM 8.0              | EC002467 |
| ETIM 9.0              | EC002467 |
| ETIM 10.0             | EC002467 |