

## Technical data sheet

### Mounting system

Part no.: 50119330

BTU 900M-D14

#### Contents

- Technical data



For illustration purposes only

## Technical data

### Basic data

|                            |                                |
|----------------------------|--------------------------------|
| Contains                   | 2x M4 x 20 screw               |
|                            | 2x M4 x 25 screw               |
|                            | 2x washers with Ø 4,3 mm each  |
| Suitable for product group | Stationary bar code readers    |
| Suitable for               | 46C series sensors             |
|                            | BCL 92 series bar code readers |
|                            | Reflector (M)TKS 30x50         |
|                            | Reflector (M)TKS 40x60         |
|                            | Reflector TKS 50x50            |

### Mechanical data

|                                             |                      |
|---------------------------------------------|----------------------|
| Standard designation, metal mounting device | Aluminum             |
|                                             | Steel, galvanized    |
| Net weight                                  | 72 g                 |
| Design of mounting device                   | Mounting system      |
| Type of fastening, at system                | For 14 mm rod        |
|                                             | Sheet-metal mounting |
| Type of fastening, at device                | Screw type           |
| Type of mounting device                     | Clampable            |
|                                             | Swiveling            |
|                                             | Turning, 360°        |
| Mounting device material                    | Metal                |

### Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 83024900 |
| ECLASS 5.1.4          | 27279202 |
| ECLASS 8.0            | 27279202 |
| ECLASS 9.0            | 27273701 |
| ECLASS 10.0           | 27273701 |
| ECLASS 11.0           | 27273701 |
| ECLASS 12.0           | 27273701 |
| ECLASS 13.0           | 27273701 |
| ECLASS 14.0           | 27273701 |
| ECLASS 15.0           | 27273701 |
| ECLASS 16.0           | 27273701 |
| ETIM 5.0              | EC002498 |
| ETIM 6.0              | EC003015 |
| ETIM 7.0              | EC003015 |
| ETIM 8.0              | EC003015 |
| ETIM 9.0              | EC003015 |
| ETIM 10.0             | EC003015 |