

Technical data sheet

Reflector

Part no.: 50104132

MTKS 30x50.1

Contents

- Technical data
- Dimensioned drawings



For illustration purposes only

Technical data

Mechanical data

Design	Rectangular
Triple reflector size	1.2 mm
Mounting dimension, width	34 mm
Mounting dimension, height	75 mm
Mounting dimension, thickness	7 mm
Reflective surface, height	44 mm
Reflective surface, width	27 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PMMA8N
Structure, active surface	Mikrotriple
Net weight	10 g
Type of fastening	Adhesive Through-hole mounting

Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

Certifications

Degree of protection	IP 67
----------------------	-------

Classification

Customs tariff number	90029000
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273601
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ECLASS 13.0	27273601
ECLASS 14.0	27273601
ECLASS 15.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467
ETIM 9.0	EC002467
ETIM 10.0	EC002467

Dimensioned drawings

All dimensions in millimeters

