

## Technical data sheet

### Distribution cable

Part no.: 150758

CB-M12-SC24

#### Contents

- Technical data
- Electrical connection

Figure can vary

## Technical data

### Basic data

Suitable for	COMPACTplus-m multiple light beam safety devices
	COMPACTplus-ml multiple light beam safety devices
	COPMACTplus-m safety light curtains

### Connection

#### Connection 1

Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	4 -pin
Encoding	A-coded
Design	Axial

#### Connection 2

Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	4 -pin
Encoding	A-coded
Design	Axial

#### Connection 3

Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	4 -pin
Encoding	A-coded
Design	Axial

### Cable properties

Number of conductors	4 Piece(s)
Shielded	No
Cable design	Distribution cable
Cable length	5,000 mm
Cable length fork 1	2,000 mm
Cable length fork 2	5,000 mm

### Certifications

Certifications	UL
----------------	----

### Classification

Customs tariff number	85444290
eCl@ss 8.0	27279218
eCl@ss 9.0	27060311
ETIM 5.0	EC001855
ETIM 6.0	EC001855

## Electrical connection

### Connection 1

Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	4 -pin
Encoding	A-coded
Design	Axial

### Connection 2

Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	4 -pin
Encoding	A-coded
Design	Axial

## Electrical connection

### Connection 3

Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	4 -pin
Encoding	A-coded
Design	Axial