

Technical data sheet

Distribution cable

Part no.: 520066

CB-M12-SCC2

Contents

- Set consists of
- Technical data
- Electrical connection

Figure can vary

Set consists of

Quantity	Part no.	Designation	Article	Description
1	150755	CB-M12-SC22	Distribution cable	Connection 1: Connector, M12, Axial, Male, A-coded, 4 -pin Connection 2: Connector, M12, Axial, Female, A-coded, 4 -pin Connection 3: Connector, M12, Axial, Female, A-coded, 4 -pin Shielded: No Cable length: 1,500 mm

Technical data

Basic data

Suitable for	COMPACTplus-m multiple light beam safety devices COMPACTplus-ml multiple light beam safety devices COPMACTplus-m safety light curtains
--------------	--

Connection

Connection 1

Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	4 -pin
Encoding	A-coded
Design	Axial

Connection 2

Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	4 -pin
Encoding	A-coded
Design	Axial

Connection 3

Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	4 -pin
Encoding	A-coded
Design	Axial

Cable properties

Number of conductors	4 Piece(s)
Shielded	No
Cable design	Distribution cable
Cable length	1,500 mm

Classification

Customs tariff number	85444290
eCl@ss 8.0	27279218
eCl@ss 9.0	27060311
ETIM 5.0	EC001855
ETIM 6.0	EC001855

Electrical connection

Connection 1

Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	4 -pin
Encoding	A-coded
Design	Axial

Connection 2

Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	4 -pin
Encoding	A-coded
Design	Axial

Electrical connection

Connection 3

Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	4 -pin
Encoding	A-coded
Design	Axial