

Technical data sheet

Adapter

Part no.: 50110649

KD 01-8-BA-PWR

Contents

- Technical data
- Electrical connection
- Accessories



For illustration purposes only

Technical data

Electrical data

Performance data

Rated operating current	2,000 mA
Rating voltage (DIN EN 60664-1)	60 V
Rated impulse voltage (DIN EN 60664-1)	800 V

Connection

Number of connections	2 Piece(s)
-----------------------	------------

Connection 1

Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	8 -pin
Encoding	A-coded
Version	Axial

Connection 2

Type of connection	Jack socket
--------------------	-------------

Cable properties

AWG	20
-----	----

Mechanical data

Width across flats	18 mm
Mating cycles, max.	> 50
Cable hole	6 ... 8 mm

Environmental data

Ambient temperature, operation	-40 ... 85 °C
--------------------------------	---------------

Certifications

Degree of protection	IP 67
----------------------	-------

Classification

Customs tariff number	85366990
ECLASS 5.1.4	27279201
ECLASS 8.0	27440104
ECLASS 9.0	27069190
ECLASS 10.0	27440106
ECLASS 11.0	27440106
ECLASS 12.0	27440106
ECLASS 13.0	27440106
ECLASS 14.0	27440106
ETIM 5.0	EC002498
ETIM 6.0	EC002498
ETIM 7.0	EC002925
ETIM 8.0	EC002925
ETIM 9.0	EC002925

Electrical connection

Connection 1

Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	8 -pin
Encoding	A-coded
Version	Axial

Connection 2

Type of connection	Jack socket
--------------------	-------------

Accessories

Power supply units

	Part no.	Designation	Article	Description
	50110748 *	NT 24-24W	Power supply unit	Type of power supply unit: Plug-in power supply unit Output: 24 V DC, 1 A Input: 110..240 V AC, 50..60 Hz

* Necessary accessories, please order separately

Accessories

Note	
	A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.