

Technical data sheet

Mirror column

Part no.: 549796

UMC-1603-S2

Contents

- Technical data
- Dimensioned drawings



For illustration purposes only

Technical data

Basic data

Series	UMC
Number of individual mirrors	3 Piece(s)
Contains	Mounting kit for floor assembly
Suitable for	MLD 500, MLD 300 multiple light beam safety devices
Type, columns and mirrors	Deflecting mirror column for multiple light beam safety devices

Functions

Functions	Adjustable, 3 directions
	Automatic resetting after mechanical impacts with special spring elements
	Easy axial alignment
	Precise alignment of the individual mirrors in all 3 axes
	Simple height adjustment of the mirrors

Mechanical data

Dimension (W x H x L)	160 mm x 1,660 mm x 149 mm
Housing material	Metal
	Plastic
Metal housing	Aluminum
Net weight	6,230 g
Housing color	Black, RAL 9005
	Yellow, RAL 1021
Type of fastening	Floor mounting
	Mounting plate
Mechanical reset function	Yes
Column height without foot	1,600 mm
Exterior mounting of accessories	Rear
Center-to-center spacing of individual mirrors	400 mm

Classification

Customs tariff number	76042990
ECLASS 5.1.4	27279207
ECLASS 8.0	27279207
ECLASS 9.0	27273605
ECLASS 10.0	27273605
ECLASS 11.0	27273605
ECLASS 12.0	27273605
ECLASS 13.0	27273605
ECLASS 14.0	27273605
ECLASS 15.0	27273605
ECLASS 16.0	27273605
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467
ETIM 9.0	EC002467
ETIM 10.0	EC002467

Dimensioned drawings

All dimensions in millimeters

