

Technical data sheet

Reflector

Part no.: 50106961

MTKS 14x23.P

Contents

- Technical data
- Dimensioned drawings



Figure can vary



Technical data

Basic data

Area of application	Pharmaceutical
---------------------	----------------

Mechanical data

Design	Rectangular
Triple reflector size	1.2 mm
Mounting dimension, width	13.6 mm
Mounting dimension, height	23 mm
Mounting dimension, thickness	4.2 mm
Reflection surface height	21 mm
Reflection surface width	11 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PES
Structure, active surface	Mikrotriple
Net weight	2 g
Type of fastening	Adhesive Through-hole mounting
Compatibility of materials	ECOLAB

Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

Certifications

Degree of protection	IP 67
----------------------	-------

Classification

Customs tariff number	90029000
eCl@ss 5.1.4	27279203
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
eCl@ss 10.0	27273601
eCl@ss 11.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467

Dimensioned drawings

All dimensions in millimeters

