

Technical data sheet

Reflector

Part no.: 50104130

MTKS 20x40.1

Contents

- Technical data
- Dimensioned drawings



Figure can vary

Technical data

Mechanical data

Design	Rectangular
Triple reflector size	1.2 mm
Mounting dimension, width	20 mm
Mounting dimension, height	60 mm
Mounting dimension, thickness	6 mm
Reflection surface height	38 mm
Reflection surface width	17 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PMMA8N
Structure, active surface	Mikrotriple
Net weight	5 g
Type of fastening	Adhesive Through-hole mounting

Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

Certifications

Degree of protection	IP 67
----------------------	-------

Classification

Customs tariff number	90029000
eCl@ss 5.1.4	27279203
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
eCl@ss 10.0	27273601
eCl@ss 11.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467

Dimensioned drawings

All dimensions in millimeters

