

## Technical data sheet

### Reflector

Part no.: 50109257

TKS 40x60.1

#### Contents

- Technical data



Figure can vary

## Technical data

### Mechanical data

Design	Rectangular
Triple reflector size	2.3 mm
Mounting dimension, width	40 mm
Mounting dimension, height	60 mm
Mounting dimension, thickness	7.2 mm
Reflection surface height	56 mm
Reflection surface width	37 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Type of fastening	Adhesive Through-hole mounting

### Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

### Certifications

Degree of protection	IP 67
----------------------	-------

### Classification

Customs tariff number	90029000
eCl@ss 5.1.4	27279203
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
eCl@ss 10.0	27273601
eCl@ss 11.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467