

Technical data sheet

Reflector

Part no.: 50112142

TK BR 53

Contents

- Technical data
- Dimensioned drawings



For illustration purposes only

Technical data

Basic data

Area of application	Food
---------------------	------

Mechanical data

Design	Rectangular
Triple reflector size	0.3 mm
Mounting dimension, width	14 mm
Mounting dimension, height	36 mm
Mounting dimension, thickness	20.3 mm
Reflective surface, height	10 mm
Reflective surface, width	29 mm
Reflector material	Plastic
Material of base material	Stainless steel
Polarization-changing	Yes
Chemical designation, reflector material	Stainless steel
Structure, active surface	Mikrotriple
Net weight	50 g
Type of fastening	Housing fit

Environmental data

Ambient temperature, operation	-30 ... 70 °C
--------------------------------	---------------

Certifications

Degree of protection	IP 67
	IP 69K

Classification

Customs tariff number	73269098
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273601
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ECLASS 13.0	27273601
ECLASS 14.0	27273601
ECLASS 15.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467
ETIM 9.0	EC002467
ETIM 10.0	EC002467

Dimensioned drawings

All dimensions in millimeters

