

Technical data sheet

Reflector

Part no.: 50129092

MTKZ 15-30 SET

Contents

- Technical data
- Dimensioned drawings



For illustration purposes only

Technical data

Basic data

| | |
|--------------|-----------|
| Contains | 100x |
| Suitable for | IPS 200i |
| | IPS 400i |
| | LSIS 472i |

Mechanical data

| | |
|--|------------------|
| Design | Round |
| Mounting dimension, thickness | 17.6 mm |
| Mounting dimension, diameter | 31 mm |
| Reflective surface, diameter | 15 mm |
| Reflector material | Plastic |
| Material of base material | Plastic |
| Polarization-changing | No |
| Chemical designation, reflector material | PA |
| Net weight | 154 g |
| Type of fastening | Clip |
| Type of reflector | Reflector |
| Suitable for bore hole diameter | 14.5 ... 15.5 mm |
| Suitable for material thickness | 0.8 ... 5 mm |

Environmental data

| | |
|--------------------------------|---------------|
| Ambient temperature, operation | -35 ... 45 °C |
| Processing temperature | 5 ... 45 °C |

Classification

| | |
|-----------------------|----------|
| Customs tariff number | 90029000 |
| ECLASS 5.1.4 | 27279203 |
| ECLASS 8.0 | 27279203 |
| ECLASS 9.0 | 27273601 |
| ECLASS 10.0 | 27273601 |
| ECLASS 11.0 | 27273601 |
| ECLASS 12.0 | 27273601 |
| ECLASS 13.0 | 27273601 |
| ECLASS 14.0 | 27273601 |
| ECLASS 15.0 | 27273601 |
| ECLASS 16.0 | 27273601 |
| ETIM 5.0 | EC002467 |
| ETIM 6.0 | EC002467 |
| ETIM 7.0 | EC002467 |
| ETIM 8.0 | EC002467 |
| ETIM 9.0 | EC002467 |
| ETIM 10.0 | EC002467 |

Dimensioned drawings

All dimensions in millimeters

