

Technical data sheet

Connection cable

Part no.: 50123532
K-D M12A-4P-30m-PVC

Contents

- Technical data
- Electrical connection




Figure can vary



Technical data

Electrical data

Performance data

Operating voltage	Max. 250 V AC/DC
-------------------	------------------

Connection

Connection 1

Type of connection	Connector
Thread size	M12
Type	Female
Handle body material	PUR
No. of pins	4 -pin
Encoding	A-coded
Design	Axial
Lock	Screw fitting, nickel-plated diecast zinc, recommended torque 0.6 Nm, self-locking

Connection 2

Type of connection	Open end
--------------------	----------

Cable properties

Number of conductors	4 Piece(s)
Wire cross section	0.34 mm ²
AWG	22
Sheathing color	Black
Shielded	No
Silicone-free	Yes
Cable design	Connection cable (open on one end)
Cable diameter (external)	5 mm
Cable length	30,000 mm
Sheathing material	PVC
Wire insulation	PVC
Properties of the outer sheathing	Free of CFC, cadmium, silicone and lead, easily machine-processable
Resistance of the outer sheathing	Good oil, gasoline and chemical resistance, flame retardant in accordance with UL 1581 VW1 / CSA FT1

Mechanical data

Bending radius, flexible laying, min.	Min. 10 x cable diameter
---------------------------------------	--------------------------

Bending radius, stationary laying, min.	Min. 5 x cable diameter
---	-------------------------

Environmental data

Ambient temperature, operation, flexible use	-5 ... 80 °C
--	--------------

Ambient temperature, operation, stationary use	-30 ... 80 °C
--	---------------

Certifications

Certifications	c UL US
	UL

Classification

Customs tariff number	85444290
eCl@ss 8.0	27279218
eCl@ss 9.0	27060311
ETIM 5.0	EC001855
ETIM 6.0	EC001855

Electrical connection


Connection 1

Type of connection	Connector
Thread size	M12
Type	Female
Handle body material	PUR
No. of pins	4 -pin
Encoding	A-coded
Design	Axial
Lock	Screw fitting, nickel-plated diecast zinc, recommended torque 0.6 Nm, self-locking

Pin

1	Brown
2	White
3	Blue
4	Black

Conductor color



Electrical connection

Connection 2

Type of connection	Open end
--------------------	----------