

## Technical data sheet

### Reflector

Part no.: 50040820

TKS 40X60

#### Contents

- Technical data
- Dimensioned drawings



Figure can vary

## Technical data

### Mechanical data

Design	Rectangular
Triple reflector size	4 mm
Mounting dimension, width	41 mm
Mounting dimension, height	60 mm
Mounting dimension, thickness	8 mm
Reflection surface height	56 mm
Reflection surface width	37 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Net weight	14 g
Type of fastening	Adhesive Through-hole mounting

### Certifications

Degree of protection	IP 67
----------------------	-------

### Classification

Customs tariff number	90029000
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273601
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467

### Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

## Dimensioned drawings

All dimensions in millimeters

TKS 40x60

