

Technical data sheet

Reflector

Part no.: 50120011

BTU 934M-D10-90

Contents

- Technical data
- Dimensioned drawings



Figure can vary

Technical data

Basic data

Suitable for	PRK retro-reflective photoelectric sensors
Pre-mounted on	TKA 30x46 reflector

Mechanical data

Design	Rectangular
Reflection surface height	30 mm
Reflection surface width	46 mm
Reflector material	Plastic
Standard designation, metal mounting device	Aluminum Steel, galvanized
Type of fastening	Clampable
Design of mounting device	Mounting system
Type of fastening, at system	For 10 mm rod Sheet-metal mounting
Type of fastening, at device	Pre-mounted reflector
Type of mounting device	Clampable Swiveling Turning, 360°
Mounting device material	Metal
ITEM-compatible	No

Environmental data

Ambient temperature, operation	-40 ... 70 °C
--------------------------------	---------------

Classification

Customs tariff number	83024900
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273701
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467

Dimensioned drawings

All dimensions in millimeters

