

Technical data sheet

Reflector

Part no.: 50003187

TK 82

Contents

- Technical data
- Dimensioned drawings



Figure can vary



Technical data

Mechanical data

Design	Round
Triple reflector size	2.3 mm
Mounting dimension, thickness	7.7 mm
Mounting dimension, diameter	84 mm
Reflection surface diameter	84 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Type of fastening	Rear side can be glued Through-hole mounting

Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

Certifications

Degree of protection	IP 67
----------------------	-------

Classification

Customs tariff number	90029000
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273601
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ECLASS 13.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467

Dimensioned drawings

All dimensions in millimeters

