

Technical data sheet

Reflector

Part no.: 50104130

MTKS 20x40.1

Contents

- Technical data
- Dimensioned drawings



Figure can vary

Technical data

Mechanical data	
Design	Rectangular
Triple reflector size	1.2 mm
Mounting dimension, width	20 mm
Mounting dimension, height	60 mm
Mounting dimension, thickness	6 mm
Reflection surface height	38 mm
Reflection surface width	17 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PMMA8N
Structure, active surface	Mikrotriple
Net weight	5 g
Type of fastening	Adhesive
	Through-hole mounting

Certifications	
Degree of protection	IP 67
Classification	
Customs tariff number	90029000
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273601
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ECLASS 13.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467

Environmental data	
Ambient temperature, operation	-40 ... 65 °C

Dimensioned drawings

All dimensions in millimeters

