

Technical data sheet

Reflector

Part no.: 50142993

BTU 934M-VKT+L-90

Contents

- Technical data
- Dimensioned drawings



For illustration purposes only

Technical data

Basic data

Suitable for product group	Switching sensors, cubic
Suitable for	PRK retro-reflective photoelectric sensors
Pre-mounted on	TKA 30x46 reflector

Mechanical data

Reflective surface, height	30 mm
Reflective surface, width	46 mm
Standard designation, metal mounting device	Aluminum Steel, galvanized
Reflector material	Plastic
Net weight	102 g
Design of mounting device	Mounting system
Type of fastening, at system	For 9-12 mm rods Sheet metal mounting bracket 3-4 mm Square rod 10 mm
Type of fastening, at device	Pre-mounted reflector
Type of mounting device	Clampable Swiveling Turning, 360°
Mounting device material	Metal

Classification

Customs tariff number	83024900
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273701
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ECLASS 13.0	27273601
ECLASS 14.0	27273601
ECLASS 15.0	27273601
ECLASS 16.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467
ETIM 9.0	EC002467
ETIM 10.0	EC002467
UNSPSC 26.08	39121551

Environmental data

Ambient temperature, operation	-40 ... 70 °C
--------------------------------	---------------

Dimensioned drawings

All dimensions in millimeters

