


Technical data sheet Interconnection cable

Part no.: 50132441

KDS U-M12-4A-M12-4A-V1-200

Contents

- Technical data
- Electrical connection
- Circuit diagrams
- Accessories



For illustration purposes only



Technical data

Basic data

| | |
|-------------|--------------------|
| Application | Chemical resistant |
|-------------|--------------------|

Connection

Connection 1

| | |
|--------------------|-----------|
| Type of connection | Connector |
| Thread size | M12 |
| Type | Female |
| No. of pins | 4 -pin |
| Encoding | A-coded |
| Version | Axial |
| Connector, LED | No |

Connection 2

| | |
|--------------------|-----------|
| Type of connection | Connector |
| Thread size | M12 |
| Type | Male |
| No. of pins | 4 -pin |
| Encoding | A-coded |
| Version | Axial |

Cable properties

| | |
|-----------------------------------|------------------------------------------------------------------------------------------------------|
| Number of conductors | 4 Piece(s) |
| Wire cross section | 0.34 mm ² |
| AWG | 22 |
| Sheathing color | Black |
| Shielded | No |
| Silicone-free | Yes |
| Cable design | Interconnection cable |
| Cable diameter (external) | 4.7 mm |
| Cable length | 20,000 mm |
| Sheathing material | PVC |
| Wire insulation | PP |
| Suitability for drag chains | No |
| Properties of the outer sheathing | Free of CFC, cadmium, silicone and lead, easily machine-processable |
| Resistance of the outer sheathing | Good oil, gasoline and chemical resistance, flame retardant in accordance with UL 1581 VW1 / CSA FT1 |

Mechanical data

| | |
|--------------------|-------|
| Width across flats | 13 mm |
| Net weight | 824 g |

Operation and display

Certifications

| | |
|----------------------|---------|
| Degree of protection | IP 65 |
| | IP 67 |
| Approvals | c UL US |
| UL file number | E366145 |

Classification

| | |
|-----------------------|----------|
| Customs tariff number | 85444290 |
| ECLASS 5.1.4 | 27279201 |
| ECLASS 8.0 | 27279218 |
| ECLASS 9.0 | 27060311 |
| ECLASS 10.0 | 27060311 |
| ECLASS 11.0 | 27060311 |
| ECLASS 12.0 | 27060311 |
| ECLASS 13.0 | 27060311 |
| ECLASS 14.0 | 27060311 |
| ECLASS 15.0 | 27060311 |
| ECLASS 16.0 | 27060311 |
| ETIM 5.0 | EC001855 |
| ETIM 6.0 | EC001855 |
| ETIM 7.0 | EC001855 |
| ETIM 8.0 | EC001855 |
| ETIM 9.0 | EC001855 |
| ETIM 10.0 | EC001855 |
| UNSPSC 26.08 | 26121604 |

Electrical connection

Connection 1

| | |
|--------------------|-----------|
| Type of connection | Connector |
| Thread size | M12 |
| Type | Female |
| No. of pins | 4 -pin |
| Encoding | A-coded |
| Version | Axial |
| Connector, LED | No |


Electrical connection

Connection 2

| | |
|--------------------|-----------|
| Type of connection | Connector |
| Thread size | M12 |
| Type | Male |
| No. of pins | 4 -pin |
| Encoding | A-coded |
| Version | Axial |

Circuit diagrams

Wiring schematic



Accessories

General

| | Part no. | Designation | Article | Description |
|--|----------|---------------|---------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| | 50132266 | TT-Set 0,6-13 | Tool | Type: Torque key Width across flats: 13 mm Torque: 0.6 N·m Material: Plastic, Stainless steel Ambient temperature: -40 ... 120 °C |

Note



A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.