

## Technical data sheet

### Reflector

Part no.: 50105990

TK 45.1

#### Contents

- Technical data
- Dimensioned drawings



For illustration purposes only

## Technical data

### Mechanical data

Design	Round
Triple reflector size	2.3 mm
Mounting dimension, thickness	7 mm
Mounting dimension, diameter	46.5 mm
Reflective surface, diameter	37 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Net weight	8 g
Type of fastening	Rear side can be glued

### Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

### Certifications

Degree of protection	IP 67
----------------------	-------

### Classification

Customs tariff number	90029000
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273601
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ECLASS 13.0	27273601
ECLASS 14.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467
ETIM 9.0	EC002467

## Dimensioned drawings

All dimensions in millimeters

