

Technical data sheet

Adapter

Part no.: 50110649

KD 01-8-BA-PWR

Contents

- Technical data
- Electrical connection
- Accessories



Figure can vary

Technical data

Electrical data

Performance data

Rated operating current	2,000 mA
Rating voltage (DIN EN 60664-1)	60 V
Rated impulse voltage (DIN EN 60664-1)	800 V

Connection

Number of connections	2 Piece(s)
-----------------------	------------

Connection 1

Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	8 -pin
Encoding	A-coded
Version	Axial

Connection 2

Type of connection	Jack socket
--------------------	-------------

Cable properties

AWG	20
-----	----

Mechanical data

Width across flats	18 mm
Mating cycles, max.	> 50
Cable hole	6 ... 8 mm

Environmental data

Ambient temperature, operation	-40 ... 85 °C
--------------------------------	---------------

Certifications

Degree of protection	IP 67
----------------------	-------

Classification

Customs tariff number	85366990
eCl@ss 5.1.4	27279201
eCl@ss 8.0	27440104
eCl@ss 9.0	27069190
eCl@ss 10.0	27440106
eCl@ss 11.0	27440106
ETIM 5.0	EC002498
ETIM 6.0	EC002498
ETIM 7.0	EC002925

Electrical connection

Connection 1


Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	8 -pin
Encoding	A-coded
Version	Axial

Connection 2

Type of connection	Jack socket
--------------------	-------------

Accessories

Power supply units

	Part no.	Designation	Article	Description
	50110748 *	NT 24-24W	Power supply unit	Type of power supply unit: Plug-in power supply unit Output: 24 V DC, 1 A Input: 110..240 V AC, 50..60 Hz

* Necessary accessories, please order separately

Accessories

Note



🔗 A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.