

Technical data sheet

Connection cable

Part no.: 150677

CB-M12-10000-5WM

Contents

- Technical data
- Electrical connection
- Circuit diagrams





Figure can vary



Technical data

Electrical data

Connection

Connection 1

Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	5 -pin
Encoding	A-coded
Version	Angled

Connection 2

Type of connection	Open end
--------------------	----------

Cable properties

Number of conductors	5 Piece(s)
Wire cross section	0.34 mm ²
Sheathing color	Black
Shielded	No
Cable design	Connection cable (open on one end)
Cable diameter (external)	6 mm
Cable length	10,000 mm
Conductor material	Copper
Sheathing material	PUR
Suitability for drag chains	No

Environmental data

Ambient temperature, operation, stationary use	-25 ... 80 °C
--	---------------

Certifications

Certifications	c UL UL
----------------	------------

Classification

Customs tariff number	85444290
eCl@ss 5.1.4	27279201
eCl@ss 8.0	27279218
eCl@ss 9.0	27060311
eCl@ss 10.0	27060311
eCl@ss 11.0	27060311
ETIM 5.0	EC001855
ETIM 6.0	EC001855
ETIM 7.0	EC001855

Electrical connection

Connection 1

Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	5 -pin
Encoding	A-coded
Version	Angled

Connection 2

Type of connection	Open end
--------------------	----------

Circuit diagrams

Wiring schematic

