

Technical data sheet

Deflecting mirror

Part no.: 50144969

US AMS 02

Contents

- Technical data
- Dimensioned drawings



For illustration purposes only

Technical data

Basic data

Suitable for	AMS 100i
Type, columns and mirrors	Surface deflecting mirror

Mechanical data

Dimension (W x H x L)	156 mm x 86 mm x 217 mm
Standard designation, metal mounting device	Steel, galvanized
Type of fastening	Through-hole mounting
Type of fastening, at system	Counter boreholes
	Screw type
	Slotted holes
Type of fastening, at device	Screw type
	Threaded holes

Classification

Customs tariff number	83024900
ECLASS 5.1.4	27279207
ECLASS 8.0	27279207
ECLASS 9.0	27273605
ECLASS 10.0	27273605
ECLASS 11.0	27273605
ECLASS 12.0	27273605
ECLASS 13.0	27273605
ECLASS 14.0	27273605
ECLASS 15.0	27273605
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467
ETIM 9.0	EC002467
ETIM 10.0	EC002467

Dimensioned drawings

All dimensions in millimeters

