


## Technical data sheet Interconnection cable

Part no.: 50106881

KB-ROD4 plus-5000

### Contents

- Technical data
- Electrical connection



For illustration purposes only

## Technical data

### Connection

#### Connection 1

Type of connection	Sub-D
Type	Female
No. of pins	9 -pin
Version	Axial

#### Connection 2

Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	5 -pin
Encoding	A-coded
Version	Axial

#### Cable properties

Shielded	Yes
Cable design	Interconnection cable
Cable length	5,000 mm
Sheathing material	PUR

### Classification

Customs tariff number	85444290
ECLASS 5.1.4	27069190
ECLASS 8.0	27069190
ECLASS 9.0	27069190
ECLASS 10.0	27060311
ECLASS 11.0	27060311
ECLASS 12.0	27060311
ECLASS 13.0	27060311
ECLASS 14.0	27060311
ECLASS 15.0	27060311
ETIM 5.0	EC001855
ETIM 6.0	EC001855
ETIM 7.0	EC001855
ETIM 8.0	EC001855
ETIM 9.0	EC001855
ETIM 10.0	EC001855

## Electrical connection

### Connection 1

Type of connection	Sub-D
Type	Female
No. of pins	9 -pin
Version	Axial

### Connection 2

Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	5 -pin
Encoding	A-coded
Version	Axial
Lock	Screw fitting, nickel-plated diecast zinc, recommended torque 0.6 Nm, self-locking