

Technical data sheet

Deflecting mirror

Part no.: 529603

UM60-300

Contents

- Technical data
- Dimensioned drawings



For illustration purposes only

Technical data

Basic data

Series	UM
Type, columns and mirrors	Deflecting mirror on the rear side

Mechanical data

Dimension (W x H x L)	25 mm x 68 mm x 370 mm
Net weight	800 g
Housing color	Yellow, RAL 1021
Type of fastening	Groove mounting
	Swivel mount
Suitable for sensor	MLC 500, MLC 300 safety light curtains
Protected field height up to	300 mm
Mirror length	360 mm


Classification

Customs tariff number	70099200
ECLASS 5.1.4	27279207
ECLASS 8.0	27279207
ECLASS 9.0	27273605
ECLASS 10.0	27273605
ECLASS 11.0	27273605
ECLASS 12.0	27273605
ECLASS 13.0	27273605
ECLASS 14.0	27273605
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467
ETIM 9.0	EC002467


Dimensioned drawings

All dimensions in millimeters


Mirror



L Length = 370 mm
SL Mirror length = 360 mm




Mounting distances



A Max. 500 mm

Dimensioned drawings


Mounting with BT-UM60 standard bracket




- A Lateral
- B Rear side
- C Adjustable at an angle (0 - 90°)

Dimensioned drawings

Mounting with BT-SSD swiveling mounting bracket



A



B

- A Rear side
- B Lateral 45°