

## Technical data sheet

### Reflector

Part no.: 50120538

TKS 40x60.1.AF

#### Contents

- Technical data



For illustration purposes only

## Technical data

### Special version

Special version	Anti-fog coating
-----------------	------------------

### Mechanical data

Design	Rectangular
Triple reflector size	2.3 mm
Mounting dimension, width	40 mm
Mounting dimension, height	60 mm
Mounting dimension, thickness	7.2 mm
Reflective surface, height	56 mm
Reflective surface, width	37 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Coating	Anti-fog
Net weight	12 g
Type of fastening	Adhesive Through-hole mounting

### Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

### Certifications

Degree of protection	IP 67
----------------------	-------

### Classification

Customs tariff number	90029000
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273601
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ECLASS 13.0	27273601
ECLASS 14.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467
ETIM 9.0	EC002467