

Technical data sheet


Connection cable

Part no.: 50141463

KD PL-M12-5A-P0-050

Contents

- Technical data
- Electrical connection
- Circuit diagrams



For illustration purposes only



Technical data

Basic data

Suitable for	MD 748i
--------------	---------

Electrical data

Performance data

Operating voltage	50 V AC / 60 V DC
-------------------	-------------------

Connection

Connection 1

Type of connection	Connector
--------------------	-----------

Thread size	M12
-------------	-----

Type	Female
------	--------

No. of pins	5 -pin
-------------	--------

Encoding	L-coded
----------	---------

Version	Axial
---------	-------

Connector, LED	No
----------------	----

Cable properties

Number of conductors	5 Piece(s)
----------------------	------------

Wire cross section	1.5 mm²
--------------------	---------

Sheathing color	Gray
-----------------	------

Shielded	No
----------	----

Cable design	Connection cable (open on one end)
--------------	------------------------------------

Cable diameter (external)	2.35 mm
---------------------------	---------

Cable length	5,000 mm
--------------	----------

Sheathing material	PUR
--------------------	-----

Wire insulation	PP
-----------------	----

Suitability for drag chains	Yes
-----------------------------	-----

Traverse rate	Max. 5 m/s with horiz. traverse path of 5m and and max. acceleration of 50m/s²
---------------	--

Environmental data

Ambient temperature, operation, flexible use	-30 ... 90 °C
--	---------------

Ambient temperature, operation, stationary use	-40 ... 90 °C
--	---------------

Certifications

Degree of protection	IP 65
----------------------	-------

IP 67

IP 69K

Certifications	c UL US
----------------	---------

Classification

Customs tariff number	85444290
-----------------------	----------

ECLASS 5.1.4	27279201
--------------	----------

ECLASS 8.0	27279218
------------	----------

ECLASS 9.0	27060311
------------	----------

ECLASS 10.0	27060311
-------------	----------

ECLASS 11.0	27060311
-------------	----------

ECLASS 12.0	27060311
-------------	----------

ECLASS 13.0	27060311
-------------	----------

ECLASS 14.0	27060311
-------------	----------

ETIM 5.0	EC001855
----------	----------

ETIM 6.0	EC001855
----------	----------

ETIM 7.0	EC001855
----------	----------

ETIM 8.0	EC001855
----------	----------

ETIM 9.0	EC001855
----------	----------

Mechanical data

Bending cycles	10,000,000 Piece(s)
----------------	---------------------

Bending radius, flexible laying, min.	Min. 7.5 x cable diameter
---------------------------------------	---------------------------


Bending radius, stationary laying, min.	Min. 4 x cable diameter
---	-------------------------

Electrical connection

Connection 1

Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	5 -pin
Encoding	L-coded
Version	Axial
Connector, LED	No

Pin	Conductor color
1	Brown
2	White
3	Blue
4	Black
5	Gray



Circuit diagrams

Wiring schematic

