

## Technical data sheet

### Reflector

Part no.: 50106961

MTKS 14x23.P

#### Contents

- Technical data
- Dimensioned drawings



For illustration purposes only



# Technical data

## Basic data

Area of application	Pharmaceutical
---------------------	----------------

## Mechanical data

Design	Rectangular
Direction-dependent	No
Triple reflector size	1.2 mm
Mounting dimension, width	13.6 mm
Mounting dimension, height	23 mm
Mounting dimension, thickness	4.2 mm
Reflective surface, height	21 mm
Reflective surface, width	11 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PES
Structure, active surface	Mikrotriple
Net weight	2 g
Type of fastening	Adhesive Through-hole mounting
Compatibility of materials	ECOLAB

## Certifications

Degree of protection	IP 67
----------------------	-------

## Classification

Customs tariff number	90029000
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273601
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ECLASS 13.0	27273601
ECLASS 14.0	27273601
ECLASS 15.0	27273601
ECLASS 16.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467
ETIM 9.0	EC002467
ETIM 10.0	EC002467
UNSPSC 26.08	39121551

## Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

# Dimensioned drawings

All dimensions in millimeters

