

Technical data sheet Reflector

Part no.: 50120019

BTU 934M-D12-90

Contents

- Technical data



For illustration purposes only

Technical data

Basic data

Suitable for product group	Switching sensors, cubic
Suitable for	PRK retro-reflective photoelectric sensors
Pre-mounted on	TKA 30x46 reflector

Mechanical data

Reflective surface, height	30 mm
Reflective surface, width	46 mm
Rod diameter	12 mm
Reflector material	Plastic
Standard designation, metal mounting device	Aluminum
	Steel, galvanized
Design of mounting device	Mounting system
Type of fastening, at system	For 12 mm rod
	Sheet-metal mounting
Type of fastening, at device	Pre-mounted reflector
Type of mounting device	Clampable
	Swiveling
	Turning, 360°
Mounting device material	Metal

Environmental data

Ambient temperature, operation	-40 ... 70 °C
--------------------------------	---------------

Classification

Customs tariff number	83024900
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273701
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ECLASS 13.0	27273601
ECLASS 14.0	27273601
ECLASS 15.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467
ETIM 9.0	EC002467
ETIM 10.0	EC002467