


Technical data sheet Interconnection cable

Part no.: 50131529

KB 900-3000

Contents

- Technical data
- Electrical connection



For illustration purposes only



Technical data

Basic data

Suitable for	BCL 900i series bar code readers
--------------	----------------------------------

Connection

Connection 1

Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	17 -pin
Encoding	A-coded
Version	Axial
Connector, LED	No

Connection 2

Type of connection	Sub-HD
Version	Axial
No. of pins	25 -pin
Type	Male

Cable properties

Number of conductors	17 Piece(s)
Sheathing color	Blue
Shielded	Yes
Cable design	Interconnection cable
Cable length	3,000 mm
Suitability for drag chains	No

Classification

Customs tariff number	85444290
ECLASS 5.1.4	27279201
ECLASS 8.0	27279218
ECLASS 9.0	27060311
ECLASS 10.0	27060311
ECLASS 11.0	27060311
ECLASS 12.0	27060311
ECLASS 13.0	27060311
ECLASS 14.0	27060311
ECLASS 15.0	27060311
ETIM 5.0	EC001855
ETIM 6.0	EC001855
ETIM 7.0	EC001855
ETIM 8.0	EC001855
ETIM 9.0	EC001855
ETIM 10.0	EC001855

Electrical connection

Connection 1

Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	17 -pin
Encoding	A-coded
Version	Axial
Connector, LED	No

Connection 2

Type of connection	Sub-HD
Version	Axial
No. of pins	25 -pin
Type	Male