

Technical data sheet

Reflector

Part no.: 50145863

TKZ 13-30 SET

Contents

- Technical data
- Dimensioned drawings



For illustration purposes only

Technical data

Basic data

Contains	100x
Suitable for	PRK retro-reflective photoelectric sensors

Mechanical data

Design	Round
Mounting dimension, thickness	17.6 mm
Mounting dimension, diameter	31 mm
Reflective surface, diameter	15 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PA
Net weight	131 g
Type of fastening	Clip
Type of reflector	Reflector
Suitable for bore hole diameter	12.5 ... 13.5 mm
Suitable for material thickness	0.8 ... 5 mm

Environmental data

Ambient temperature, operation	-35 ... 45 °C
Processing temperature	5 ... 45 °C

Classification

Customs tariff number	90029000
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273601
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ECLASS 13.0	27273601
ECLASS 14.0	27273601
ECLASS 15.0	27273601
ECLASS 16.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467
ETIM 9.0	EC002467
ETIM 10.0	EC002467
UNSPSC 26.08	39121551

Dimensioned drawings

All dimensions in millimeters

