

Technical data sheet

Reflector

Part no.: 50129076

TKZ 25

Contents

- Technical data



For illustration purposes only

Technical data

Mechanical data

Design	Round
Direction-dependent	No
Triple reflector size	2.3 mm
Mounting dimension, thickness	7 mm
Mounting dimension, diameter	26.2 mm
Reflective surface, diameter	23 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PMMA
Structure, active surface	Triple
Net weight	3 g
Type of fastening	Clip
Suitable for bore hole diameter	6 ... 7 mm
Suitable for material thickness	0.5 ... ∞

Environmental data

Ambient temperature, operation	-40 ... 65 °C
Processing temperature	0 ... 70 °C

Classification

Customs tariff number	90029000
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273601
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ECLASS 13.0	27273601
ECLASS 14.0	27273601
ECLASS 15.0	27273601
ECLASS 16.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467
ETIM 9.0	EC002467
ETIM 10.0	EC002467
UNSPSC 26.08	39121551