

Technical data sheet

Clamp

Part no.: 50111500

MC 012K-LS

Contents

- Technical data



For illustration purposes only

Technical data

Basic data

Suitable for product group	Switching sensors, cylindrical
Suitable for	212 series sensors
	412 series sensors
	Sensors with M12 design

Mechanical data

Inner diameter	12 mm
Chemical designation, plastic mounting devices	Polyamide (PA 66)
Design of mounting device	Mounting clamp
Type of fastening, at system	Through-hole mounting
Type of fastening, at device	Clampable with limit stop
Type of mounting device	Rigid
Mounting device material	Plastic

Environmental data

Ambient temperature, operation	0 ... 80 °C
--------------------------------	-------------

Classification

Customs tariff number	39174000
ECLASS 5.1.4	27279202
ECLASS 8.0	27279202
ECLASS 9.0	27273701
ECLASS 10.0	27273701
ECLASS 11.0	27273701
ECLASS 12.0	27273701
ECLASS 13.0	27273701
ECLASS 14.0	27273701
ECLASS 15.0	27273701
ETIM 5.0	EC002498
ETIM 6.0	EC003015
ETIM 7.0	EC003015
ETIM 8.0	EC003015
ETIM 9.0	EC003015