

## Technical data sheet

### Clamp

Part no.: 50111497

MC 008K

#### Contents

- Technical data
- Dimensioned drawings



For illustration purposes only

## Technical data

### Basic data

Suitable for product group	Switching sensors, cylindrical
Suitable for	208 series sensors
	Sensors with M8 design

### Mechanical data

Inner diameter	8 mm
Chemical designation, plastic mounting devices	Polyamide (PA 66)
Net weight	4 g
Design of mounting device	Mounting clamp
Type of fastening, at system	Through-hole mounting
Type of fastening, at device	Clampable
Type of mounting device	Rigid
Mounting device material	Plastic

### Environmental data

Ambient temperature, operation	0 ... 80 °C
--------------------------------	-------------

### Classification

Customs tariff number	39174000
ECLASS 5.1.4	27279202
ECLASS 8.0	27279202
ECLASS 9.0	27273701
ECLASS 10.0	27273701
ECLASS 11.0	27273701
ECLASS 12.0	27273701
ECLASS 13.0	27273701
ECLASS 14.0	27273701
ECLASS 15.0	27273701
ECLASS 16.0	27273701
ETIM 5.0	EC002498
ETIM 6.0	EC003015
ETIM 7.0	EC003015
ETIM 8.0	EC003015
ETIM 9.0	EC003015
ETIM 10.0	EC003015
UNSPSC 26.08	31242100

## Dimensioned drawings

All dimensions in millimeters

