

## Technical data sheet

### Reflector

Part no.: 50130290

TK 100 x100-Set



#### Contents

- Set consists of
- Technical data
- Dimensioned drawings



For illustration purposes only

## Set consists of

	Quantity	Part no.	Designation	Article	Description
	2	50009419	BT 910M	Mounting bracket	Design of mounting device: Angle, L-shape Fastening, at system: Through-hole mounting Mounting bracket, at device: Screw type Type of mounting device: Rigid Material: Metal
	1	50003192	TK 100x100	Reflector	Design: Rectangular Triple reflector size: 4 mm Reflective surface: 96 mm x 96 mm Material: Plastic Base material: Plastic Chemical designation of the material: PMMA8N Fastening: Rear side can be glued

## Technical data

### Mechanical data

Design	Rectangular
Triple reflector size	4 mm
Mounting dimension, width	99.4 mm
Mounting dimension, height	99.4 mm
Mounting dimension, thickness	8.7 mm
Reflective surface, height	96 mm
Reflective surface, width	96 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Net weight	61 g
Type of fastening	Rear side can be glued Supplied mounting bracket

### Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

### Certifications

Degree of protection	IP 67
----------------------	-------

### Classification

Customs tariff number	90029000
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273601
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ECLASS 13.0	27273601
ECLASS 14.0	27273601
ECLASS 15.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467
ETIM 9.0	EC002467
ETIM 10.0	EC002467

## Dimensioned drawings

All dimensions in millimeters

