

## Technical data sheet

### Mobile bar code reader

Part no.: 50141806  
IT 1400g PDF-2-USB-KIT

#### Contents

- Technical data
- Electrical connection
- Operation and display
- Accessories



For illustration purposes only



## Technical data

### Basic data

|          |                                    |
|----------|------------------------------------|
| Series   | IT14xx                             |
| Contains | 1x USB interconnection cable 1.5 m |

### Read data

|                      |                             |
|----------------------|-----------------------------|
| Code types, readable | 2/5 Interleaved             |
|                      | Codabar                     |
|                      | Codablock                   |
|                      | Code 128                    |
|                      | Code 39                     |
|                      | Code 93                     |
|                      | EAN 128                     |
|                      | EAN 8/13                    |
|                      | EAN Addendum                |
|                      | GS1 Databar                 |
|                      | GS1 Databar Expanded        |
|                      | GS1 Databar Limited         |
|                      | GS1 Databar Omnidirectional |
|                      | GS1 Databar Stacked         |
|                      | GS1 Databar Truncated       |
|                      | Micro PDF                   |
|                      | PDF417                      |
|                      | UPC                         |

### Optical data

|                               |                    |
|-------------------------------|--------------------|
| Reading distance              | 37 ... 370 mm      |
| Light source                  | LED, Red           |
| LED group                     | 1                  |
| Camera resolution, horizontal | 640 px             |
| Camera resolution, vertical   | 480 px             |
| Bar code contrast (PCS)       | 35 %               |
| Modulus size                  | 0.127 ... 0.508 mm |

### Electrical data

|                         |                 |
|-------------------------|-----------------|
| <b>Performance data</b> |                 |
| Supply voltage $U_B$    | 4 ... 5.5 V, DC |
| Power consumption, max. | 2 W             |

### Interface

|               |             |
|---------------|-------------|
| Type          | RS 232, USB |
| <b>RS 232</b> |             |
| Function      | Process     |

### USB

|          |         |
|----------|---------|
| Function | Process |
|----------|---------|

### Connection

#### Connection 1

|                    |      |
|--------------------|------|
| Type of connection | RJ41 |
|--------------------|------|

### Mechanical data

|                       |                        |
|-----------------------|------------------------|
| Dimension (W x H x L) | 66 mm x 43 mm x 180 mm |
| Housing material      | Plastic                |
| Plastic housing       | UL 94-V0               |
| Net weight            | 119 g                  |

### Environmental data

|                                    |                |
|------------------------------------|----------------|
| Ambient temperature, operation     | 0 ... 40 °C    |
| Ambient temperature, storage       | -40 ... 60 °C  |
| Relative humidity (non-condensing) | 0 ... 95 %     |
| Drop height                        | 1.5 m          |
| Measurements relative to           | Concrete floor |

### Certifications

|                      |         |
|----------------------|---------|
| Degree of protection | IP 42   |
| Approvals            | c UL US |

### Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 84719000 |
| ECLASS 5.1.4          | 27280101 |
| ECLASS 8.0            | 27280101 |
| ECLASS 9.0            | 27280101 |
| ECLASS 10.0           | 27280101 |
| ECLASS 11.0           | 27280101 |
| ECLASS 12.0           | 27280101 |
| ECLASS 13.0           | 27280101 |
| ECLASS 14.0           | 27280101 |
| ECLASS 15.0           | 27280101 |
| ETIM 5.0              | EC002550 |
| ETIM 6.0              | EC002550 |
| ETIM 7.0              | EC002550 |
| ETIM 8.0              | EC002550 |
| ETIM 9.0              | EC002550 |
| ETIM 10.0             | EC002550 |

## Electrical connection

### Connection 1

|                    |                         |
|--------------------|-------------------------|
| Function           | Configuration interface |
|                    | Data interface          |
|                    | Service interface       |
| Type of connection | RJ41                    |

## Electrical connection

| Pin | Pin assignment           |
|-----|--------------------------|
| 1   | Shield                   |
| 2   | Cable ID                 |
| 3   | GND                      |
| 4   | TxD RS 232 / n.c. USB    |
| 5   | RxD RS 232 / n.c. USB    |
| 6   | CTS RS 232 / n.c. USB    |
| 7   | +5 V DC                  |
| 8   | RTS RS 232 / n.c. USB    |
| 9   | n.c. RS 232 / Data + USB |
| 10  | n.c. RS 232 / Data - USB |




## Operation and display


| LED | Display            | Meaning            |
|-----|--------------------|--------------------|
| 1   | Green, 1x flashing | Reading successful |
|     | Red                | No reading result  |

## Accessories


### Connection technology - Connection unit

|  | Part no. | Designation              | Article                 | Description   |
|--|----------|--------------------------|-------------------------|---|
|  | 50112891 | MA 248i Profinet Gateway | Modular connection unit | Supply voltage: 18 ... 30 V<br>Current consumption, max.: 300 mA<br>Interface: PROFINET, RS 232<br>Connections: 6 Piece(s)<br>Degree of protection: IP 65 |

### Connection technology - Interconnection cables

|  | Part no. | Designation   | Article               | Description   |
|--|----------|---------------|-----------------------|---|
|  | 50113397 | KB JST-HS-300 | Interconnection cable | Suitable for interface: RS 232<br>Connection 1: JST ZHR connector<br>Connection 2: Sub-D, Axial, Male, 9 -pin<br>Shielded: Yes<br>Cable length: 300 mm<br>Sheathing material: PUR |

### Connection technology - Y distribution cables

|  | Part no. | Designation     | Article               | Description  |
|--|----------|-----------------|-----------------------|--|
|  | 50114517 | KB 232-1 IT190x | Interconnection cable | Suitable for interface: RS 232, TTL<br>Connection 1: RJ41<br>Connection 2: Sub-D, Axial, Female, 9 -pin<br>Connection 3: Connector, Pluggable, Axial, Female, 2 -pin<br>Shielded: Yes<br>Cable length: 3,000 mm<br>Sheathing material: PVC |

## Accessories

### Note



🔗 A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.