

Technical data sheet

Connection unit

Part no.: 50148809

MK 3007

Contents

- Technical data
- Dimensioned drawings
- Electrical connection



For illustration purposes only

Technical data

Basic data

Suitable for	BPS 3007i
--------------	-----------

Interface

Type	SSI
------	-----

Connection

Number of connections	3 Piece(s)
-----------------------	------------

Connection 1

Function	PWR / SW IN / OUT
Type of connection	Terminal
No. of pins	5 -pin

Connection 2

Function	HOST / BUS IN
Type of connection	Terminal
No. of pins	5 -pin

Connection 4

Type of connection	USB
--------------------	-----

Mechanical data



Design	Cubic
Dimension (W x H x L)	64 mm x 83.5 mm x 43.5 mm
Housing material	Metal
Metal housing	Diecast aluminum
Net weight	186 g
Housing color	Red

Classification

Customs tariff number	84733080
ECLASS 5.1.4	27280190
ECLASS 8.0	27280190
ECLASS 9.0	27279090
ECLASS 10.0	27280192
ECLASS 11.0	27280191
ECLASS 12.0	27280191
ECLASS 13.0	27280191
ECLASS 14.0	27280191
ECLASS 15.0	27280191
ETIM 5.0	EC002498
ETIM 6.0	EC003015
ETIM 7.0	EC003015
ETIM 8.0	EC003015
ETIM 9.0	EC003015
ETIM 10.0	EC003015

Dimensioned drawings

All dimensions in millimeters



Electrical connection

Connection 1

Function	PWR / SW IN / OUT
Type of connection	Terminal
Cable gland	M16
No. of pins	5 -pin

Electrical connection

Terminal	Assignment
1	SWIO 2
2	SWIO 1
3	VIN
4	GNDIN
5	FE

Connection 2

Function	HOST / BUS IN
Type of connection	Terminal
Cable gland	M16
No. of pins	5 -pin

Terminal	Assignment
1	DATA+
2	DATA-
3	n.c.
4	CLK-
5	CLK+

Connection 4

Type of connection	USB
--------------------	-----