

## Technical data sheet Interconnection cable

Part no.: 50109881

KB ET-5000-SA-RJ45

### Contents

- Technical data
- Electrical connection



Figure can vary



## Technical data

### Basic data

Suitable for interface	Ethernet
------------------------	----------

### Connection

#### Connection 1

Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	4 -pin
Encoding	D-coded
Design	Axial

#### Connection 2

Type of connection	RJ45
Type	Male
No. of pins	4 -pin
Design	Axial

### Cable properties

Number of conductors	4 Piece(s)
Sheathing color	Green
Shielded	Yes
Cable design	Interconnection cable
Cable diameter (external)	6.5 mm
Cable length	5,000 mm
Sheathing material	PUR

### Classification

Customs tariff number	85444290
eCl@ss 8.0	27279218
eCl@ss 9.0	27060311
ETIM 5.0	EC001855
ETIM 6.0	EC001855

## Electrical connection

### Connection 1

Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	4 -pin
Encoding	D-coded
Design	Axial

### Connection 2

Type of connection	RJ45
--------------------	------