

Technical data sheet

Reflector set

Part no.: 50125455

TKS 40x60.A

Contents

- Technical data



For illustration purposes only

Technical data

Basic data

Contains	10x
----------	-----

Mechanical data

Design	Rectangular
--------	-------------

Triple reflector size	2.3 mm
-----------------------	--------

Mounting dimension, width	40.4 mm
---------------------------	---------

Mounting dimension, height	60 mm
----------------------------	-------

Mounting dimension, thickness	7.2 mm
-------------------------------	--------

Reflective surface, height	55.8 mm
----------------------------	---------

Reflective surface, width	36.8 mm
---------------------------	---------

Reflector material	Plastic
--------------------	---------

Material of base material	Plastic
---------------------------	---------

Polarization-changing	Yes
-----------------------	-----

Chemical designation, reflector material	PMMA8N
--	--------

Structure, active surface	Triple
---------------------------	--------

Net weight	36 g
------------	------

Type of fastening	Adhesive
-------------------	----------

	Screw type
--	------------

Environmental data

Ambient temperature, operation	-20 ... 65 °C
--------------------------------	---------------

Classification

Customs tariff number	90029000
-----------------------	----------

ECLASS 5.1.4	27279203
--------------	----------

ECLASS 8.0	27279203
------------	----------

ECLASS 9.0	27273601
------------	----------

ECLASS 10.0	27273601
-------------	----------

ECLASS 11.0	27273601
-------------	----------

ECLASS 12.0	27273601
-------------	----------

ECLASS 13.0	27273601
-------------	----------

ECLASS 14.0	27273601
-------------	----------

ECLASS 15.0	27273601
-------------	----------

ETIM 5.0	EC002467
----------	----------

ETIM 6.0	EC002467
----------	----------

ETIM 7.0	EC002467
----------	----------

ETIM 8.0	EC002467
----------	----------

ETIM 9.0	EC002467
----------	----------

ETIM 10.0	EC002467
-----------	----------