

Technical data sheet

Reflector

Part no.: 50130291

TK 40 x180.1-Set



Contents

- Set consists of
- Technical data
- Dimensioned drawings



For illustration purposes only

Set consists of

	Quantity	Part no.	Designation	Article	Description
	2	50009419	BT 910M	Mounting bracket	Design of mounting device: Angle, L-shape Fastening, at system: Through-hole mounting Mounting bracket, at device: Screw type Type of mounting device: Rigid Material: Metal
	1	50022811	TK 40X180.1	Reflector	Design: Rectangular Triple reflector size: 3 mm Reflective surface: 36 mm x 176 mm Material: Plastic Base material: Plastic Chemical designation of the material: PMMA8N Fastening: Rear side can be glued

Technical data

Mechanical data

Design	Rectangular
Direction-dependent	No
Triple reflector size	3 mm
Mounting dimension, width	41 mm
Mounting dimension, height	181 mm
Mounting dimension, thickness	8.2 mm
Reflective surface, height	176 mm
Reflective surface, width	36 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Net weight	39 g
Type of fastening	Rear side can be glued

Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

Certifications

Degree of protection	IP 67
----------------------	-------

Classification

Customs tariff number	90029000
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273601
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ECLASS 13.0	27273601
ECLASS 14.0	27273601
ECLASS 15.0	27273601
ECLASS 16.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467
ETIM 9.0	EC002467
ETIM 10.0	EC002467
UNSPSC 26.08	39121551

Dimensioned drawings

All dimensions in millimeters

