

## Technical data sheet


### Connection cable

Part no.: 50108139

KB-ROD4-CP-10000

#### Contents

- Technical data
- Electrical connection



For illustration purposes only



## Technical data

### Basic data

Application	Chemical resistant
Parameter memory	Yes

### Electrical data

#### Performance data

Operating voltage	30 V AC/DC
-------------------	------------

### Connection

#### Connection 1

Type of connection	Sub-D
Connector, LED	No
Type	Female
No. of pins	15 -pin
Version	Axial

#### Connection 2

Type of connection	Open end
--------------------	----------

#### Cable properties

Number of conductors	15 Piece(s)
Shielded	Yes
Cable design	Connection cable (open on one end)
Cable length	10,000 mm
Sheathing material	PVC
Suitability for drag chains	No

### Mechanical data

Net weight	1,159 g
------------	---------

### Operation and display

### Certifications

US patents	US 7,696,468 B
------------	----------------

### Classification

Customs tariff number	85444290
ECLASS 5.1.4	27279201
ECLASS 8.0	27279218
ECLASS 9.0	27060311
ECLASS 10.0	27060311
ECLASS 11.0	27060311
ECLASS 12.0	27060311
ECLASS 13.0	27060311
ECLASS 14.0	27060311
ECLASS 15.0	27060311
ECLASS 16.0	27060311
ETIM 5.0	EC001855
ETIM 6.0	EC001855
ETIM 7.0	EC001855
ETIM 8.0	EC001855
ETIM 9.0	EC001855
ETIM 10.0	EC001855

## Electrical connection

### Connection 1

Type of connection	Sub-D
Connector, LED	No
Type	Female
No. of pins	15 -pin
Version	Axial

### Connection 2

Type of connection	Open end
--------------------	----------